

# PREMIUM NITRILE

## Gloveworks®

### INDUSTRIAL BLUE NITRILE GLOVES



#### Recommended Uses



#### General Description

|                 |              |                 |                          |
|-----------------|--------------|-----------------|--------------------------|
| <b>Material</b> | Nitrile      | <b>Type</b>     | Non-Sterile              |
| <b>Color</b>    | Blue         | <b>Usage</b>    | Single Use               |
| <b>Shape</b>    | Ambidextrous | <b>Interior</b> | Powder Free              |
| <b>Sizes</b>    | S - XXL      | <b>Exterior</b> | Textured/Micro-roughened |
| <b>Cuff</b>     | Beaded       | <b>Process</b>  | Chlorinated              |

#### Product Codes

|                 |           |
|-----------------|-----------|
| <b>Small</b>    | INPF42100 |
| <b>Medium</b>   | INPF44100 |
| <b>Large</b>    | INPF46100 |
| <b>X-Large</b>  | INPF48100 |
| <b>XX-Large</b> | INPF49100 |

#### Packaging

|                  |                    |
|------------------|--------------------|
| <b>Box</b>       | 100 Gloves Per Box |
| <b>Box Dims</b>  | 220 x 125 x 68 mm  |
| <b>Case</b>      | 10 Boxes Per Case  |
| <b>Case Dims</b> | 354 x 260 x 230 mm |

#### Physical Properties

|                                |              |
|--------------------------------|--------------|
| <b>Tensile Strength</b>        | 14 Mpa (min) |
| <b>Tensile Strength (Aged)</b> | 14 Mpa (min) |
| <b>Powder Content</b>          | < 2 mg       |
| <b>FDA Listing</b>             | N/A          |
| <b>Elongation</b>              | 500%         |
| <b>Elongation (Aged)</b>       | 400%         |
| <b>Protein Content</b>         | N/A          |
| <b>AQL Level</b>               | 4.0          |

#### Dimensions

|                  |             |                 |            |
|------------------|-------------|-----------------|------------|
| <b>Weight</b>    | 5.8 ± 0.2 g | <b>Length</b>   | 240 ± 5 mm |
| <b>Thickness</b> |             | <b>Width</b>    |            |
| <b>Cuff</b>      | 4 ± 1 mil   | <b>Small</b>    | 80 ± 5 mm  |
| <b>Palm</b>      | 5 ± 1 mil   | <b>Medium</b>   | 90 ± 5 mm  |
| <b>Finger</b>    | 6 ± 1 mil   | <b>Large</b>    | 103 ± 5 mm |
|                  |             | <b>X-Large</b>  | 108 ± 5 mm |
|                  |             | <b>XX-Large</b> | 117 ± 5 mm |

#### Barcodes

|                                                                                                                  |                                                                                                                  |                                                                                                                  |                                                                                                                    |                                                                                                                      |
|------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------|
| <br>6 97383 70121 3<br>S Box  | <br>6 97383 70122 0<br>M Box  | <br>6 97383 70123 7<br>L Box  | <br>6 97383 70124 4<br>XL Box  | <br>6 97383 70125 1<br>XXL Box  |
| <br>6 97383 71121 2<br>S Case | <br>6 97383 71122 9<br>M Case | <br>6 97383 71123 6<br>L Case | <br>6 97383 71124 3<br>XL Case | <br>6 97383 71125 0<br>XXL Case |

